


This fully enclosed curing chamber features 360 degree shielding for maximum UV protection. Just place your IntelliRay or SunRay on top of the oven and start curing - *no tools required*!

The Rayven includes a door interlock for use with the IntelliRay system, which automatically causes the unit's shutter to close when the door is opened. Dual rear panel D-sub connectors allow pass through of IntelliRay control signals for use with a PC, PLC, shutter control foot pedal, external interlock, etc. The oven also has an adjustable height curing tray which allows for 5 repeatable curing distances, and a door mounted lamp-ON indicator.





Specifications:

Category	Parameter	Value	Conditions/Notes
General	Model	RAYVEN Curing Oven	
	Part Number	UV1080	
	Cooling	Forced air w/ louvers	Channeled from lamp head
	Interconnect Cable	Dual 15 position DSUB	Male/Female, 1.25 ft.
Dimensions			
H x W x D (inches)	Inside	9" x 9" x 10.4"	w/ adjustable shelf
	Outside	11.8" x 11.6" x 12.1"	D= 13.3" w/ door handle
	Weight (lbs.)	9 Pounds	Without lamp head
Cure Distance	Shelf Positions	1.75", 3.5", 5.25", 7.0"	Bottom of lamp to shelf
(inches)	Distance to floor	9"	Bottom of lamp to floor

Uvitron International • 150 Front St, Unit 4 • West Springfield, MA 01089 (413) 731-7835 • www.uvitron.com • info@uvitron.com • Rev 113018